

# MAUD OB

## Sporty and ultra-light sneaker for her

The MAUD medical shoes are the ultimate in comfort and safety. With SR slip resistance, aremovable footbed, 3D mesh, breathable upper, and lightweight design, these shoes are designed to keep you safe and comfortable.

Upper	Mesh
Lining	Mesh
Footbed	SJ foam footbed
Outsole	Phylon/Rubber (NBR)
Category	OB / SRA, E
Size range	EU 35-42 / UK 3.0-8.0 / US 5.5-10.5 JPN 21.5-26.5 / KOR 230-270
Sample weight	0.280 kg
Norms	ASTM F2892:2024 EN ISO 20347:2012































## 3D mesh

Three-dimensional produced distance mesh to provide increased moisture and temperature management.



## Removable insole

Renew your insole at a regular base or use your own orthopedic insoles for a higher comfort.



## **Breathable upper**

Increased moisture and temperature management for extended wearer comfort.



#### Oxygrip / SJ Grip

Rubber outsoles with Oxytraction® technology provide excellent traction on both dry and wet floors and meet SRC (SRA+ SRB) standards.



#### **SRA slip resistance**

Slip resistance is one of the most important features of safety and occupational footwear. SRA slip resistant soles are tested on a ceramic tile with dilute soap solution.



#### **Industries:**

Catering, Cleaning, Food & beverages, Medical

### **Environments:**

Dry environment

## **Maintenance instructions:**

To extend the life of your shoes, we recommend to clean them regularly and to protect them with adequate products. Do not dry your shoes on a radiator, nor nearby a heat source.

	Description	Measure unit	Result	EN ISO 20347
Upper	Mesh			
	Upper: permeability to water vapor	mg/cm²/h	1.4	≥ 0.8
	Upper: water vapor coefficient	mg/cm²	15.5	≥ 15
Lining	Mesh			
	Lining: permeability to water vapor	mg/cm²/h	28.9	≥ 2
	Lining: water vapor coefficient	mg/cm²	231.3	≥ 20
Footbed	SJ foam footbed			
	Footbed: abrasion resistance (dry/wet) (cycles)	cycles	25600/12800	25600/12800
Outsole	Phylon/Rubber (NBR)			
	Outsole abrasion resistance (volume loss)	mm³	81.0	≤ 150
	Outsole slip resistance SRA: heel	friction	0.48	≥ 0.28
	Outsole slip resistance SRA: flat	friction	0.45	≥ 0.32
	Outsole slip resistance SRB: heel	friction	N/A	≥ 0.13
	Outsole slip resistance SRB: flat	friction	N/A	≥ 0.18
	Antistatic value	MegaOhm	N/A	0.1 - 1000
	ESD value	MegaOhm	N/A	0.1 - 100
	Heel energy absorption	J	34	≥ 20

Sample size: 38

Our shoes are constantly evolving, the technical data above may change. All product names and brand Safety Jogger, are registered and may not be used or reproduced in any format, without written consent from us.



